


760237997 | EHD12-DM-24LC-LS-AS-ULL

EHD ULL Multimode OM4, MPO-12 distribution module, 24LC to 2x12f
MPOs pinned, dust plugs



Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Series	EHD

General Specifications

Functionality	Breakout
Color, front	Aqua
Color, rear	Black
Interface, front	LC/UPC
Interface, rear	MPO
Interface Feature, rear	Key up/down Pinned
Polarity	Method A Pairs, straight
Shuttered	No
Total Fibers, quantity	24

Dimensions

Height	12.45 mm 0.49 in
Width	169.67 mm 6.68 in
Depth	115.32 mm 4.54 in

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM4, LazrSPEED® 550

760237997 | EHD12-DM-24LC-LS-AS-ULL

Insertion Loss, maximum 0.35 dB

Environmental Specifications

Qualification Standards IEC 61753-1 | TIA-568.3-D

Safety Standard CE | CSA | UL

Packaging and Weights

Packaging quantity 1

Weight, net 0.136 kg | 0.3 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

