# 760238000 | EHD24-DM-24LC-WB-B-ULL



EHD ULL Multimode OM5 Wideband MPO-24 distribution module, 24LC to 1x24f MPOs unpinned, dust plugs

### **Product Classification**

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

PortfolioCommScope®Product TypeFiber moduleProduct BrandSYSTIMAX ULL

Product Series EHD

# General Specifications

Functionality Breakout

Color, front Lime green

 Color, rear
 Gray

 Interface, front
 LC/UPC

 Interface, rear
 MPO

Interface Feature, rear Key up/up | MPO Non-Pinned

**Polarity** Method B Enhanced (ULL)

Shuttered No Total Fibers, quantity 24

#### **Dimensions**

 Height
 12.45 mm | 0.49 in

 Width
 169.67 mm | 6.68 in

 Depth
 115.32 mm | 4.54 in

# **Optical Specifications**

Fiber Mode Multimode

**COMMSCOPE®** 

# 760238000 | EHD24-DM-24LC-WB-B-ULL

Fiber Type OM5, LazrSPEED® wideband

**Insertion Loss, maximum** 0.35 dB

## **Environmental Specifications**

**Qualification Standards** IEC 61753-1 | TIA-568.3-D

Safety Standard CE | CSA | UL

## Packaging and Weights

Packaging quantity 1

**Weight, net** 0.136 kg | 0.3 lb

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

