



Fiber Optic Panel, 1U, unloaded, for holding up to 3 LGX/1000 modules, black

Product Classification

Regional Availability	Asia
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	1000-style

General Specifications

Application	Accepts three LGX/1000 footprint panels/cassettes
Cable Exit Location	Rear, left side Rear, right side
Color	Black
Growth Configuration	Unloaded
Module/Adapter Pack Slots, quantity	3
Modules Included, quantity	0
Rack Type	EIA 19 in
Rack Units	1
Shelf Movement	Sliding
Splice Tray Capacity, quantity	2
Splice Trays Included, quantity	0

Dimensions

Height	43.7 mm 1.72 in
Width	482.6 mm 19 in
Depth	308.1 mm 12.13 in

Material Specifications

Finish	Powder coated
---------------	---------------

760241725

Material Type Steel

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

