

760242495 | DM12-24LC-LS-A



G2 MPOptimate® Multimode OM4 MPO-12 Distribution Module, 24LC to 2x12f MPO's pinned, internal shutters

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Series	G2

General Specifications

Color, front	Aqua
Color, rear	Black
Interface, front	LC
Interface Feature, front	Standard
Interface, rear	MPO Pinned
Interface Feature, rear	Key up/down
Polarity	Method A Pairs, straight
Shuttered	Yes
Total Fibers, quantity	24

Dimensions

Height	26.42 mm 1.04 in
Width	96.52 mm 3.8 in
Depth	117.35 mm 4.62 in

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM4
Insertion Loss, maximum	0.35 dB

Environmental Specifications

Qualification Standards IEC 61753-1 | TIA-568.3-D

Safety Standard CE | CSA | UL

Packaging and Weights

Packaging quantity 1

Weight, net 0.113 kg | 0.249 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

Classification

Above maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant/Exempted

