

760242974 | 360DMiP-24LCA-SM

G2 Singlemode APC Module, 24 LC fibers (12 duplex ports) ,iPatch Ready



Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber module

General Specifications

Functionality	Breakout
Adapters, quantity, front	12
Adapters, quantity, rear	2
Color, front	Green
Color, rear	Lime green
Data Module Type	Standard
Intelligence Type	iPatch® ready
Interface, front	LC/APC
Interface, rear	MPO
Interface Feature, rear	Pinned Reduced footprint
Shuttered	Yes
Total Fibers, quantity	24
Total Ports, quantity, front	24

Dimensions

Height	30.48 mm 1.2 in
Width	91.44 mm 3.6 in
Depth	116.84 mm 4.6 in

Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.652.D and G.657.A1, TeraSPEED® OS2
Insertion Loss Change, mating	0.3 dB
Insertion Loss Change, temperature	0.3 dB
Insertion Loss, maximum	1.05 dB
Return Loss, minimum	62 dB

Environmental Specifications

Safety Standard	UL cUL
------------------------	----------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Insertion Loss Change, mating	Maximum insertion loss change after 500 matings
Insertion Loss Change, temperature	Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)