937232-000 | FIST-GPS2-M-NNN-R



FIST® GPS2 Fiber Chassis with pigtail storage for holding up to 4 GPST Patch/Splice Trays, unloaded, 3RU, ETSI width, gray

Product Classification

Regional Availability EMEA

Portfolio CommScope®

Product Type Fiber patch/splice chassis

Product Brand FIST®

Product Series FIST-GPS2

General Specifications

Functionality Patching | Splicing

Application Used in FIST-GR3-style frames only

Color Gray

Growth ConfigurationUnloadedInterface, frontUnloaded

Rack Type ETSI 600 mm

Rack Units 3

Shelf Movement Sliding

Total Ports, quantity 0

Dimensions

 Height
 133.35 mm | 5.25 in

 Width
 531 mm | 20.906 in

Material Specifications

Finish Powder coated

Material Type Galvanized steel

Environmental Specifications



937232-000 | FIST-GPS2-M-NNN-R

Operating Temperature $-5 \,^{\circ}\text{C} \text{ to } +45 \,^{\circ}\text{C} \text{ (+23 °F to +113 °F)}$

Storage Temperature $-30 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-22 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Relative Humidity Up to 93%, non-condensing

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

