

CY0684-000 | OCM6-SP11GL2-18DB1-NZ



OCM6 Fiber Optic Splitter Module, Planar, one 1x16 Splitter, singlemode, LC/APC, symmetrical split ratio, butt style, 1.8 m pigtailed

Product Classification

Regional Availability	Australia/New Zealand
Portfolio	CommScope®
Product Type	Splitter module
Product Series	OCM6

General Specifications

Device Type	Standard VAM
Functionality	Splitting
Technology Type	Planar lightwave circuit (PLC)
Application	For use with BUDI wall boxes
Circuits, quantity	1
Distribution Type	1 x 16 splitter
Interface, Input	LC
Interface Feature, Input	APC
Interface, Output	LC
Interface Feature, Output	APC
Split Ratio	Symmetrical
Splitter, quantity	1

Dimensions

Height	130 mm 5.118 in
Width	49.8 mm 1.961 in
Depth	16.5 mm 0.65 in
Pigtail Length, Input	1.8 m 5.906 ft

CY0684-000 | OCM6-SP11GL2-18DB1-NZ

Pigtail Length, Output 1.8 m | 5.906 ft
Pigtail Diameter 1.8 mm | 0.071 in

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

Classification

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

