

# CY8048-000 | OCM6-SP114S2-72CI1

OCM6 Fiber Optic Splitter Module, Planar, one 1x4 Splitter, singlemode, SC /APC, symmetrical split ratio, in-line style, 72 cm pigtailed



## Product Classification

<b>Regional Availability</b>	EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Splitter module
<b>Product Series</b>	OCM6

## General Specifications

<b>Device Type</b>	Standard VAM
<b>Functionality</b>	Splitting
<b>Technology Type</b>	Planar lightwave circuit (PLC)
<b>Application</b>	For use with BUDI wall boxes
<b>Circuits, quantity</b>	1
<b>Distribution Type</b>	1 x 4 splitter
<b>Interface, Input</b>	SC/APC
<b>Interface, Output</b>	SC/APC
<b>Split Ratio</b>	Symmetrical
<b>Splitter, quantity</b>	1

## Dimensions

<b>Height</b>	130 mm   5.118 in
<b>Width</b>	49.8 mm   1.961 in
<b>Depth</b>	16.5 mm   0.65 in
<b>Pigtail Length, Output</b>	0.72 m   2.362 ft
<b>Pigtail Diameter</b>	1.8 mm   0.071 in

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

