CZ3250-000 | OCM6-SP12GL2-19DB1



OCM6 Fiber Optic Splitter Module, Planar, one 2x16 Splitter, singlemode, LC/APC, symmetrical split ratio, butt style, 1.9 m pigtails

Product Classification

Regional Availability EMEA

PortfolioCommScope®Product TypeSplitter module

Product Series OCM6

General Specifications

Device Type Standard VAM

Functionality Splitting

Technology Type Planar lightwave circuit (PLC)

Application For use with BUDI wall boxes

Circuits, quantity 1

Distribution Type 2 x 16 splitter

Interface, InputLC/APCInterface, OutputLC/APC

Split Ratio Symmetrical

Splitter, quantity 1

Dimensions

 Height
 130 mm | 5.118 in

 Width
 49.8 mm | 1.961 in

 Depth
 16.5 mm | 0.65 in

 Pigtail Length, Input
 1.9 m | 6.234 ft

 Pigtail Length, Output
 1.9 m | 6.234 ft

 Pigtail Diameter
 1.8 mm | 0.071 in



CZ3250-000 | OCM6-SP12GL2-19DB1

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

