

EG6171-000 | OCM6-SP12WL2-72CB1

OCM6 Fiber Optic Splitter Module, Planar, one 2x32 Splitter, singlemode, LC/APC, symmetrical split ratio, butt style, 72 cm pigtails



Product Classification

| | |
|------------------------------|-----------------|
| Regional Availability | EMEA |
| Portfolio | CommScope® |
| Product Type | Splitter module |
| Product Series | OCM6 |

General Specifications

| | |
|---------------------------|--------------------------------|
| Device Type | Standard VAM |
| Functionality | Splitting |
| Technology Type | Planar lightwave circuit (PLC) |
| Application | For use with BUDI wall boxes |
| Circuits, quantity | 1 |
| Distribution Type | 2 x 32 splitter |
| Interface, Input | LC/APC |
| Interface, Output | LC/APC |
| Split Ratio | Symmetrical |
| Splitter, quantity | 1 |

Dimensions

| | |
|-------------------------------|--------------------|
| Height | 130 mm 5.118 in |
| Width | 49.8 mm 1.961 in |
| Depth | 16.5 mm 0.65 in |
| Pigtail Length, Input | 0.72 m 2.362 ft |
| Pigtail Length, Output | 0.72 m 2.362 ft |
| Pigtail Diameter | 1.8 mm 0.071 in |

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

