

EG8276-000 | OCM6-SA622NS2-72CB1

OCM6 Fiber Optic Splitter Module, FBT, six 2x2 Splitters, singlemode, SC /APC output only, symmetrical split ratio, butt style, 72 cm pigtails



Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Splitter module
Product Series	OCM6

General Specifications

Device Type	Standard VAM
Functionality	Splitting
Technology Type	Fused biconic tapered
Application	For use with BUDI wall boxes
Circuits, quantity	6
Distribution Type	2 x 2 splitter
Interface, Input	Stub tail
Interface, Output	SC/APC
Split Ratio	Symmetrical
Splitter, quantity	6

Dimensions

Height	130 mm 5.118 in
Width	49.8 mm 1.961 in
Depth	16.5 mm 0.65 in
Pigtail Length, Input	2.1 m 6.89 ft
Pigtail Length, Output	2.1 m 6.89 ft
Pigtail Diameter	1.8 mm 0.071 in

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

