

EG9252-001 | OCM1-SP11800S2-AP



OCM1 LGX Style Fiber Optic Splitter Module, Planar, one 1x8 Splitter, singlemode, SC/APC, symmetrical split ratio

Product Classification

| | |
|------------------------------|-----------------|
| Regional Availability | Asia |
| Portfolio | CommScope® |
| Product Type | Splitter module |
| Product Series | LGX OCM1 |

General Specifications

| | |
|----------------------------------|--------------------------------|
| Device Type | Standard VAM |
| Functionality | Splitting |
| Technology Type | Planar lightwave circuit (PLC) |
| Access | Front |
| Application | For use with LGX panels |
| Circuits, quantity | 1 |
| Distribution Type | 1 x 8 splitter |
| Interface, Input | SC |
| Interface Feature, Input | APC |
| Interface, Output | SC |
| Interface Feature, Output | APC |
| Split Ratio | Symmetrical |
| Splitter, quantity | 1 |

Dimensions

| | |
|---------------|--------------------|
| Height | 129.54 mm 5.1 in |
| Width | 58.42 mm 2.3 in |
| Depth | 127 mm 5 in |

Packaging and Weights

Packaging quantity 1

Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

REACH-SVHC

ROHS

Classification

Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

