

Fiber adapter plate, 1U, unpopulated, for holding up to 4 Quick-Fit modules

OBSOLETE

This product was discontinued on: October 1, 2019

Product Classification

Regional Availability	Australia/New Zealand EMEA
Portfolio	NETCONNECT®
Product Type	Fiber adapter plate

General Specifications

Color	Black
--------------	-------

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	39.624 mm 1.56 in

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	5%–95%, non-condensing
Environmental Space	Indoor
Flammability Rating	UL 94 V-0

Packaging and Weights

Packaging quantity	1
Packaging Type	Bag Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance

1-1671373-1

ROHS

Compliant

