



G2 Modular Cassette with 12 LC LazrSPEED® 550 Pigtails

OBSOLETE

Replaced By:

760109470
360G2 Cartridge 12-LC-LS-AQ-PIGTAILS

360G2 Multimode OM4 Fiber Cassette 12 LC, with pigtails, iPatch Ready

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Fiber cassette with pigtails
Product Brand	LazrSPEED®

General Specifications

Adapter Color	Aqua
Interface, front	LC/UPC
Interface, rear	Stranded pigtail
Total Fibers, quantity	12
Total Ports, quantity, front	12

Dimensions

Height	30.48 mm 1.2 in
Width	91.44 mm 3.6 in
Depth	119.38 mm 4.7 in
Pigtail Length	1.5 m 4.921 ft

Optical Specifications

Fiber Type	OM4, LazrSPEED® 550
Insertion Loss, typical	0.27 dB
Return Loss, minimum	20 dB

Packaging and Weights

Regulatory Compliance/Certifications

Classification

Designed, manufactured and/or distributed under this quality management system

Included Products

700207004 - LazrSPEED® LC Multiport Shuttered Adapter, Aqua, Single Pack
MFA-LC12-AQ-SHUTTERED