



G2 Modular Cassette with 6 SC OptiSPEED® Multimode Pigtails, Type B

OBSOLETE

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Fiber cassette with pigtails
Product Brand	OptiSPEED®

General Specifications

Adapter Color	Beige
Interface, front	SC/UPC
Interface, rear	Stranded pigtail
Total Fibers, quantity	6
Total Ports, quantity, front	6

Dimensions

Height	30.48 mm 1.2 in
Width	91.44 mm 3.6 in
Depth	119.38 mm 4.7 in
Pigtail Length	1.5 m 4.921 ft

Optical Specifications

Fiber Type	OM1
Insertion Loss, typical	0.3 dB
Return Loss, minimum	20 dB

Environmental Specifications

760034090 | MODG2-6SC-MM-PT-B

Safety Standard UL

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Included Products

700206956	–	OptiSPEED® SC Multiport Shuttered Adapter, Beige, Single Pack
MFA-SC06-BG-SHUTTERED		