

# 760082578 | RK4P52-36A



Equipment Rack, 4-Post, 36 in (914 mm) D x 8 ft (2438 mm) H - 19 in (482.6 mm) Alu (52U) 12-24 Tapped Rails, Black

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	4 post rack

## General Specifications

<b>Color</b>	Black
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	52
<b>Rail Mounting Hole</b>	#12-24

## Dimensions

<b>Height</b>	2,438.4 mm   96 in
<b>Channel Width</b>	76.2 mm   3 in
<b>Width</b>	518.16 mm   20.4 in
<b>Depth</b>	1,219.2 mm   48 in
<b>Dimensional Standards</b>	EIA-310-E

## Material Specifications

<b>Finish</b>	Powder-coated, textured
<b>Material Type</b>	Aluminum

## Mechanical Specifications

<b>Static Load Rating</b>	907.2 kg   2,000.031 lb
---------------------------	-------------------------

## Packaging and Weights

<b>Included</b>	Base pan   Forty #12-24 x 1/2 in mounting screws   Four vertical rack rails   Instruction sheet   Twenty four 3/8 in split lock washers   Twenty four 3/8-16 UNC x 1 in hex head
-----------------	----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

# 760082578 | RK4P52-36A

---

bolts | Twenty four 3/8-16 hex nuts | Two extruded base angles | Two extruded top angles | Upper plate support

<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Flat packed
<b>Weight, net</b>	46.27 kg   102.008 lb

## Regulatory Compliance/Certifications

### Agency

CHINA-ROHS  
ISO 9001:2015  
REACH-SVHC  
ROHS  
UK-ROHS

### Classification

Below maximum concentration value  
Designed, manufactured and/or distributed under this quality management system  
Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)  
Compliant  
Compliant

