760162040 | SHELF-ADJ-19-1U-24X36



Shelf, Adj, 19"x1Ux24-36D, 125# AI

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Shelf

General Specifications

Color	Black
Rack Type	EIA 19 in
Rack Units	1

Dimensions

Height	43.7 mm 1.72 in
Width	482.6 mm 19 in
Depth	610 mm 24.016 in
Adjustable Depth, maximum	914.4 mm 36 in
Dimensional Standards	EIA-310-D

Material Specifications

Finish	Powder-coated, textured
Material Type	Steel

Mechanical Specifications

Static Load Rating	57 kg	125.663 lb
3	5.	

Packaging and Weights

Included	Eight #10-32 pan head screws Eight #12-24 x 1/2 in mounting screws Eight KEPS nuts Fixed shelf
Packaging guantity	1

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2024



760162040 | SHELF-ADJ-19-1U-24X36

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 3, 2024

