

760242402 | ODF-FF19CM-SPL



Rack with cable managers and Splice Cabinet

Product Classification

Regional Availability North America

Product Type Frame

General Specifications

Access Front | Rear

Application For use with any 19" rack mount panels

Color Black

Growth Configuration Unloaded

Mounting Concrete floor | Raised floor

Dimensions

Height 2,133.6 mm | 84 in

Width 1,339.09 mm | 52.72 in

Depth 609.6 mm | 24 in

Material Specifications

Finish Powder coated

Material Type Steel

Environmental Specifications

Environmental Space Indoor

Qualification Standards Seismic rating, zone 4

Packaging and Weights

760242402 | ODF-FF19CM-SPL

Included	Cable management
Packaging quantity	1
Packaging Type	Crate Pallet
Weight, net	199.581 kg 440 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

