



G2 Splice Cassette, 12LC/UPC with internal shutters, OS2, with pigtails

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber cassette with pigtails
Product Series	G2

## General Specifications

Color, front	Blue
Interface, front	LC/UPC
Interface, rear	Stranded pigtail
Polarity	Pairs, straight
Shuttered	Yes
Total Fibers, quantity	12

## Dimensions

Height	26.416 mm   1.04 in
Width	96.52 mm   3.8 in
Depth	165.354 mm   6.51 in

## Material Specifications

Alignment Sleeve Material	Zirconia
---------------------------	----------

## Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2
Insertion Loss, maximum	0.25 dB

Return Loss, minimum50 dB

Environmental Specifications

Qualification StandardsIEC 61753-1 | TIA-568.3-D

Safety StandardUL

Packaging and Weights

IncludedSMOUV holder | SMOUV splice protection

Packaging quantity1

Weight, net0.126 kg | 0.278 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

