

# CHD-4U-W



SYSTIMAX® CHD 4U sliding tray fiber panel, accepts (48) CHD ULL modules, splice cassettes or MPO panels, providing up to 288 duplex LC ports or up to 288 MPO ports, white, High Speed Migration

This product will be discontinued on: December 31, 2025

Replaced By:

760255955 PPL-4U-W	Propel 4RU sliding tray white fiber panel, accepts Propel ULL modules or adapter packs, providing up to 288 duplex LC ports, 288 MPO ports or 576 SN ports (1152f)
-----------------------	--

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	CHD

## General Specifications

Application	Accepts 48 CHD Universal Modules, or CHD MPO/LC adapter packs
Color	White
Interface, front	Unloaded
Rack Units	4
Shelf Movement	Sliding
Total Ports, quantity	0

## Dimensions

Height	177.8 mm   7 in
Width	482.6 mm   19 in
Depth	538.48 mm   21.2 in

## Packaging and Weights

Weight, net	15.604 kg   34.4 lb
-------------	---------------------

# CHD-4U-W

---

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

