

MX6-BSPL-1440-U7



OMX® Splice Cabinet, up to 1440 fiber splices, overhead bay, enters from above, exit up

Product Classification

Regional Availability	Australia/New Zealand EMEA Latin America North America
Product Type	Fiber entrance cabinet
Product Brand	OMX600®
Product Series	OMX

General Specifications

Access	Front
Cable Entry Location	Top
Cable Exit Location	Top
Color	Black
Mounting	Concrete floor
Splice Trays Included, quantity	0
Splicing Capacity Note	up to 5184 ribbon fibers
Splicing Capacity, maximum	5184

Dimensions

Height	2134 mm 84.016 in
Width	600 mm 23.622 in
Depth	300 mm 11.811 in

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

Regulatory Compliance/Certifications

MX6-BSPL-1440-U7

Agency

CHINA-ROHS
REACH-SVHC
ROHS

Classification

Below maximum concentration value
Compliant as per SVHC revision on www.commscope.com/ProductCompliance
Compliant

