

# MX6-SPL6030-1440-D



OMX® Splice Cabinet, up to 5184 fiber splices (ribbon cables), exit down, Putty white, 2.2 mts

## Replaced By:

MX6-SPL6030-A-D7Z4 OMX® Splice Cabinet, up to 5184 fiber splices (ribbon cables), exit down, Putty white, 7 ft

## Product Classification

<b>Regional Availability</b>	Australia/New Zealand   EMEA   Latin America   North America
<b>Product Type</b>	Fiber entrance cabinet
<b>Product Brand</b>	OMX600®
<b>Product Series</b>	OMX

## General Specifications

<b>Access</b>	Front
<b>Cable Entry Location</b>	Bottom
<b>Cable Exit Location</b>	Bottom
<b>Color</b>	Putty white
<b>Mounting</b>	Raised floor
<b>Splice Trays Included, quantity</b>	0
<b>Splicing Capacity Note</b>	up to 5184 ribbon fibers
<b>Splicing Capacity, maximum</b>	5184

## Dimensions

<b>Height</b>	2200 mm   86.614 in
<b>Width</b>	600 mm   23.622 in
<b>Depth</b>	300 mm   11.811 in

# MX6-SPL6030-1440-D

---

## Environmental Specifications

**Environmental Space** Indoor

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted

