

MX6-SPL6030-1440-U



OMX® Splice Cabinet, up to 5184 fiber splices (ribbon cables), exit up, Putty white, 2.2 mts

Replaced By:

MX6-SPL6030-A-U7Z4 OMX® Splice Cabinet, up to 5184 fiber splices (ribbon cables), exit up, Putty white, 7 ft

Product Classification

Regional Availability	Australia/New Zealand EMEA Latin America North America
Product Type	Fiber entrance cabinet
Product Brand	OMX600®
Product Series	OMX

General Specifications

Access	Front
Cable Entry Location	Top
Cable Exit Location	Top
Color	Putty white
Mounting	Concrete floor
Splice Trays Included, quantity	0
Splicing Capacity Note	up to 5184 ribbon fibers
Splicing Capacity, maximum	5184

Dimensions

Height	2200 mm 86.614 in
Width	600 mm 23.622 in
Depth	300 mm 11.811 in

MX6-SPL6030-1440-U

Environmental Specifications

Environmental Space Indoor

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted

