



GS3 1650 C2 Copper Splice Closure, cold applied, for cables up to 900 pairs

- Cold applied buried and pedestal splice closure system providing a fast, simple way to seal and encapsulate telephone cable splices
- Material is composed of several layers of specially blended polymers and gels and an aluminum moisture vapor barrier layer
- Outer compression wrap provides excellent mechanical strength and superior protection from forces such as impact and abrasion
- Innovative Urethane Delivery System drives encapsulant into the core of the cable, providing protection superior to that of traditional poured urethane systems

Product Classification

Regional Availability	Latin America North America
Product Type	Sealing sheet closure
Product Series	GS3

General Specifications

Cable Sealing Type	Multilayer gel sealing sheet
Closure Style	In-line
Color	Black
Required Encapsulant, minimum	5000 g 11.023 lb
Splicing Capacity, maximum	900

Dimensions

Splice Bundle Diameter, maximum	134.62 mm 5.3 in
Sheet Opening, nominal	533.4 mm 21 in

Environmental Specifications

Environmental Space	Buried
----------------------------	--------

Packaging and Weights

Packaging quantity	1
Packaging Type	Bag Carton

Regulatory Compliance/Certifications

Agency

CHINA-ROHS
REACH-SVHC
ROHS

Classification

Below maximum concentration value
Compliant as per SVHC revision on www.commscope.com/ProductCompliance
Compliant

