

525118-000 | XAGA-1000-200/65-500A340

XAGA® 1000 Copper Closure, pressurized, heat shrink, 500 mm sheath opening, 200 mm splice bundle diameter



- High performance heat-shrinkable closure for both maintenance and new constructions
- Suitable for use with all standard copper connector systems
- Full range of closures to suit all copper cable sizes

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

| | |
|------------------------------|---------------------------------|
| Regional Availability | EMEA |
| Product Type | Pressurized heat shrink closure |
| Product Brand | XAGA® |
| Product Series | XAGA 1000 |

General Specifications

| | |
|--------------------------------|---|
| Application | For use with Polyethylene and metal jacketed cables |
| Branch-off Clip | To be ordered separately |
| Cable Capacity, maximum | 4 |
| Cable Sealing Type | Hotmelt adhesive |
| Closure Style | In-line |
| Color | Black |
| Mounting | Duct Manhole |
| Splice Protection Type | Metal canister with valve |

Dimensions

| | |
|--|--------------------|
| Single Cable Diameter, minimum | 65 mm 2.559 in |
| Splice Bundle Diameter, maximum | 200 mm 7.874 in |
| Sheath Opening, nominal | 500 mm 19.685 in |

Dimension Drawing



Material Specifications

Material Type Fiber-reinforced multi-layer sealing sleeve

Environmental Specifications

Environmental Space Aerial | Below ground | Buried

Packaging and Weights

Included Abrasive strip | Aluminum closing strip | Aluminum foil | Cleaning tissues | Flexible stainless steel channels | Heatshrinkable sleeve | Metal canister | Shield continuity wire | Underclips | Valve hardware

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

| Agency | Classification |
|------------|---|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

