565299-000 | XAGA-530-75/15-300



XAGA® 530 Copper Closure, unpressurized, heat shrink, 300 mm sheath opening, 75 mm splice bundle diameter

- Full range of closures to suit all copper cable sizes
- High performance heat-shrinkable closure for both maintenance and new constructions
- Suitable for use with all standard copper connector systems

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Regional Availability EMEA

Product Type Unpressurized heat shrink closure

Product Brand XAGA®
Product Series XAGA 530

General Specifications

Application For use with Polyethylene and metal jacketed cables

Branch-off ClipTo be ordered seperately

Cable Capacity, maximum 3

Cable Sealing Type Hotmelt adhesive

Color In-line Black

Mounting Duct | Manhole


Splice Protection Type Hygroscopic liner | Laminated cardboard liner

Dimensions

Single Cable Diameter, minimum15 mm | 0.591 inSplice Bundle Diameter, maximum75 mm | 2.953 inSheath Opening, nominal300 mm | 11.811 in

Dimension Drawing

Page 1 of 2



Material Specifications

Material Type Fiber-reinforced multi-layer sealing sleeve

Environmental Specifications

Environmental Space Aerial | Below ground | Buried

Packaging and Weights

Included Abrasive strip | Aluminum closing strip | Aluminum foil | Cleaning tissues | Flexible

stainless steel channels | Heatshrinkable sleeve | Metal canister | Shield continuity

wire | Underclips | Valve hardware

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



