## 574488-000 | FOSC450-6DGD1504NN2T-U23



FOSC® 450 Fiber Optic Splice Closure, Gel Cable sealing, with integrated dense WDDM, B sz, 12 chan. adptr, 1501 nm starting wavelength

- Single-ended, O-ring sealed dome closure for splicing feeder and distribution cables
- Gel cable sealing technology allows easy adding or removing of a wide size range of cables
- Compatible with most common cable types: e.g. loose tube, central core, ribbon fiber
- FOSC splice trays hinged for access to any splice without disturbing other trays
- Closure can be used in aerial, pedestal and underground (up to 5 meters) environments
- Compatible with CommScope's CWDM modules and optical splitter trays

#### **Product Classification**

 Regional Availability
 Latin America | North America

 Product Type
 Single-ended, round fiber closure

Product Brand FOSC®
Product Series FOSC 450

### General Specifications

Cable Entry Drop Port StyleRoundCable Entry Main Port StyleRound

Cable Ports Quantity, total6 round portsCable Sealing TypeCompressed gel

Closure Sealing Type Dome-to-base clamp with O-ring

Closure Style Single-ended

ColorBlackFlash Test ValveNoneGround Feed-throughNone

Mounting Pole | Strand | Wall

Network Area Type Feeder

Splice Tray Included, quantity 6

Splicing Type, Supported Mass fusion | Single fusion

**Dimensions** 

**Length** 610 mm | 24.016 in **Diameter** 180 mm | 7.087 in

COMMSCSPE®

# 574488-000 | FOSC450-6DGD1504NN2T-U23

Diameter, with clamp232 mm9.134 inMain Cable Diameter, maximum25 mm0.984 in

Material Specifications

Material Type Impact-resistant polymer

## **Environmental Specifications**

Environmental SpaceBelow ground| BuriedQualification StandardsIEC 61300, 5 m waterhead

#### Packaging and Weights

**Included** Multiplexer (2)

Packaging quantity

Packaging Type Box | Carton

Weight, net 5.5 kg | 12.125 lb

### Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

