

760158592 | OVRHDRACKVCM



3 in (76 mm) Channel x 9.4in (239 mm) H - 19 in (482.6 mm) Overhead Patch Panel Rack (4U) 3/8 Sq Punch, with Mini Vertical Cable Management, Black

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Mini-rack, overhead

General Specifications

Color	Black
Rack Type	EIA 19 in
Rack Units	4
Height	238.76 mm 9.4 in
Channel Width	76.2 mm 3 in
Width	596.9 mm 23.5 in
Depth	264.16 mm 10.4 in
Dimensional Standards	EIA-310-E

Material Specifications

Finish	Powder-coated, textured
Material Type	Steel

Mechanical Specifications

Static Load Rating	27.2 kg 59.966 lb
---------------------------	---------------------

Packaging and Weights

Included	Instruction sheet Mini vertical cable management, with cover Six 5/16-18 hex nuts Six 5/16-18 hex screws Sixteen M6 cage nuts Sixteen M6 mounting screws Three 1/4-20 hex screws Three flat washers Two flat washers Two ladder clamp brackets Two mounting brackets
-----------------	--

760158592 | OVRHDRACKVCM

Packaging quantity	1
Packaging Type	Assembled
Weight, net	3.64 kg 8.025 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

