

760169581 | OVRHDRACK6U



3 in (76 mm) Channel x 9.5 in (239 mm) H - 19 in (482.6 mm) Overhead Patch Panel Rack (6U) 3/8 Sq Punch, Black

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Mini-rack, overhead

General Specifications

Color	Black
Rack Type	EIA 19 in
Rack Units	6

Dimensions

Height	327.66 mm 12.9 in
Channel Width	76.2 mm 3 in
Width	500.38 mm 19.7 in
Depth	76.2 mm 3 in
Dimensional Standards	EIA-310-D

Material Specifications

Finish	Powder-coated, textured
Material Type	Steel

Mechanical Specifications

Static Load Rating	27.2 kg 59.966 lb
---------------------------	---------------------

Packaging and Weights

Included	Instruction sheet Patch panel rack Six 5/16-18 hex nuts Six 5/16-18 hex screws Twenty-four M6 cage nuts Twenty-four M6 mounting screws Two flat washers Two ladder clamp brackets Two mounting brackets Two rack support brackets
-----------------	---

760169581 | OVRHDRACK6U

Packaging quantity 1
Packaging Type Assembled

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

