

760169599 | OVRHDRACKVCM6U



3 in (76 mm) Channel x 12.9 in (327.66 mm) H - 19 in (482.6 mm)
Overhead Patch Panel Rack (6U) 3/8 Sq Punch, with Mini Vertical Cable
Management, Black

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Mini-rack, overhead

General Specifications

Color	Black
Rack Type	EIA 19 in
Rack Units	6
Height	327.66 mm 12.9 in
Channel Width	76.2 mm 3 in
Width	596.9 mm 23.5 in
Depth	264.16 mm 10.4 in
Dimensional Standards	EIA-310-D

Material Specifications

Finish	Powder-coated, textured
Material Type	Steel

Mechanical Specifications

Load Rating	27.216 kg 60 lb
--------------------	-------------------

Packaging and Weights

Included	Instruction sheet Mini vertical cable management, with cover Patch panel rack Six 5/16-18 hex nuts Six 5/16-18 hex screws Twenty-four M6 cage nuts Twenty-four M6 mounting screws Two flat washers Two ladder clamp brackets Two mounting brackets Two rack support brackets
-----------------	--

Packaging quantity 1
Packaging Type Assembled

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

