# 760237942 | EHD-SP-24LC-SMR-AS-ULL



EHD ULL 24f LC UPC ribbon splice cassette Singlemode, includes 2, FST-ACC006 mass fusion splice sleeves

#### **Product Classification**

Portfolio SYSTIMAX®

**Product Type** Fiber cassette with ribbon pigtail

Product Brand SYSTIMAX ULL

Product Series EHD

## General Specifications

Adapters, quantity, front 24

Adapters, quantity, rear 0

Color, front Blue

Interface, front LC/UPC

Interface, rear Ribbon pigtail

**Polarity** Method A | Pairs, straight

Total Fibers, quantity 24

Total Ports, quantity, front 24

#### **Dimensions**

 Height
 12.446 mm | 0.49 in

 Width
 169.672 mm | 6.68 in

 Depth
 163.83 mm | 6.45 in

## Optical Specifications

Fiber Type G.657.A2

# **Environmental Specifications**



# 760237942 | EHD-SP-24LC-SMR-AS-ULL

Safety Standard cUL US 1863

Packaging and Weights

Packaging quantity

**Weight, net** 0.454 kg | 1 lb

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



#### Included Products

FST-ACC006 - Fiber Optic Protective Splice Sleeve, 12f mass fusion, 5

pack



## Fiber Optic Protective Splice Sleeve, 12f mass fusion, 5 pack

#### **Product Classification**

Regional Availability North America

**Product Type** Fiber protection sleeve

General Specifications

**Splicing Type** Heat shrink, mass fusion

## **Environmental Specifications**

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F}$ )

## Packaging and Weights

Packaging quantity 5

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

