

760242111 | PNL-CS-24LCV



Standard Density (SD) splicing cassette 24LC OM5, no pigtail

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber cassette |

General Specifications

| | |
|-------------------------------------|------------|
| Adapter Color | Lime green |
| Interface, front | LC/UPC |
| Interface, rear | No pigtail |
| Total Fibers, quantity | 24 |
| Total Ports, quantity, front | 12 |

Dimensions

| | |
|---------------|----------------------|
| Height | 28.956 mm 1.14 in |
| Width | 104.648 mm 4.12 in |
| Depth | 165.354 mm 6.51 in |

Optical Specifications

| | |
|-------------------|-----------|
| Fiber Mode | Multimode |
|-------------------|-----------|

Environmental Specifications

| | |
|------------------------|----|
| Safety Standard | UL |
|------------------------|----|

Packaging and Weights

| | |
|---------------------------|---|
| Packaging quantity | 1 |
|---------------------------|---|

Regulatory Compliance/Certifications

| Agency | Classification |
|--------|----------------|
|--------|----------------|

760242111 | PNL-CS-24LCV

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

