



CHD ULL Singlemode Splice Cassette, 12LC, with dust plugs and ribbon pigtails

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber cassette with ribbon pigtail
<b>Product Brand</b>	SYSTIMAX ULL
<b>Product Series</b>	CHD

## General Specifications

<b>Color, front</b>	Blue
<b>Interface, front</b>	LC/UPC
<b>Interface, rear</b>	Ribbon pigtail
<b>Polarity</b>	Method A   Pairs, straight
<b>Shuttered</b>	No
<b>Total Fibers, quantity</b>	12

## Dimensions

<b>Height</b>	12.446 mm   0.49 in
<b>Width</b>	83.82 mm   3.3 in
<b>Depth</b>	184.658 mm   7.27 in

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	G.657.A2
<b>Insertion Loss, maximum</b>	0.25 dB

# 760244825 | CHD-SP-12LC-SMR-AS-ULL

---

## Environmental Specifications

**Qualification Standards** IEC 61753-1 | TIA-568.3-D

**Safety Standard** CE | CSA | UL

## Packaging and Weights

**Included** Mass Fusion Splice Protection Sleeves

**Packaging quantity** 1

**Weight, net** 0.095 kg | 0.21 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
RCM	Compliant to electrical safety & telecommunications requirements
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## Included Products

FST-ACC006 – Fiber Optic Protective Splice Sleeve, 12f mass fusion, 1 each