



XAGA® 1000 Copper Closure, pressurized, heat shrink, 900 mm sheath opening, 200 mm splice bundle diameter

- High performance heat-shrinkable closure for both maintenance and new constructions
- Suitable for use with all standard copper connector systems
- Full range of closures to suit all copper cable sizes

## OBSOLETE

This product was discontinued on: June 30, 2022

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Pressurized heat shrink closure
<b>Product Brand</b>	XAGA®
<b>Product Series</b>	XAGA 1000

## General Specifications

<b>Application</b>	For use with Polyethylene and metal jacketed cables
<b>Branch-off Clip</b>	To be ordered separately
<b>Cable Capacity, maximum</b>	4
<b>Cable Sealing Type</b>	Hotmelt adhesive
<b>Closure Style</b>	In-line
<b>Color</b>	Black
<b>Mounting</b>	Duct   Manhole
<b>Splice Protection Type</b>	Metal canister with valve

## Dimensions

<b>Single Cable Diameter, minimum</b>	65 mm   2.559 in
<b>Splice Bundle Diameter, maximum</b>	200 mm   7.874 in
<b>Sheath Opening, nominal</b>	900 mm   35.433 in

## Dimension Drawing



## Material Specifications

**Material Type** Fiber-reinforced multi-layer sealing sleeve

## Environmental Specifications

**Environmental Space** Aerial | Below ground | Buried

## Packaging and Weights

**Included** Abrasive strip | Aluminum closing strip | Aluminum foil | Cleaning tissues | Flexible stainless steel channels | Heatshrinkable sleeve | Metal canister | Shield continuity wire | Underclips | Valve hardware

**Packaging quantity** 1

**Packaging Type** Bag | Carton

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

