



FOSC® Gel Sealing Kit for round splice closure port, sealing 1 cable with diameter between 11 and 14 mm

- Unique gel-based mechanical sealing option used on fiber splice closure ports for blown, standard, mini- and micro-cables
- Allows usage of multiple cable drops in a single closure outlet port, thus significantly increasing existing cable capacity
- Ideal for fiber cables with thin outer jackets that are difficult to seal with standard heat shrinkable sleeves

Product Classification

| | |
|-----------------------|---------------|
| Regional Availability | EMEA |
| Product Type | Cable sealing |
| Product Brand | FOSC® |
| Product Series | FOSC 400G |

General Specifications

| | |
|-------------------------|---------------------------------------|
| Application | For use with FOSC-400G Fiber closures |
| Cable Capacity, maximum | 1 |
| Color | Black |

Dimensions

| | |
|--------------------------------|------------------|
| Single Cable Diameter, maximum | 14 mm 0.551 in |
| Single Cable Diameter, minimum | 11 mm 0.433 in |

Packaging and Weights

| | |
|--------------------|---|
| Included | Cable termination brackets Dummy plugs Multi-out gel seal |
| Packaging quantity | 1 |

Regulatory Compliance/Certifications

| Agency | Classification |
|------------|---|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |

UK-ROHS

Compliant

