

CV6797-000 | TENIO-SKG3-7/10



TENIO™ Cable Gel Seal kit, 3 cable outlets, 7 to 10 mm diameter per cable outlet

Product Classification

Regional Availability	EMEA
Product Type	Cable sealing
Product Series	TENIO

General Specifications

Application	For use with TENIO Fiber closures
Cable Capacity, maximum	3
Color	Black

Dimensions

Single Cable Diameter, maximum	10 mm 0.394 in
Single Cable Diameter, minimum	7 mm 0.276 in

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ROHS	Compliant
UK-ROHS	Compliant

