

# CW6616-000 | TENIO-SKG4-3/6

---



TENIO™ Cable Gel Seal kit, 4 cable outlets, 3 to 6 mm diameter per cable outlet

## Product Classification

|                              |               |
|------------------------------|---------------|
| <b>Regional Availability</b> | EMEA          |
| <b>Product Type</b>          | Cable sealing |
| <b>Product Series</b>        | TENIO         |

## General Specifications

|                                |                                   |
|--------------------------------|-----------------------------------|
| <b>Application</b>             | For use with TENIO Fiber closures |
| <b>Cable Capacity, maximum</b> | 4                                 |
| <b>Color</b>                   | Black                             |

## Dimensions

|                                       |                 |
|---------------------------------------|-----------------|
| <b>Single Cable Diameter, maximum</b> | 6 mm   0.236 in |
| <b>Single Cable Diameter, minimum</b> | 3 mm   0.118 in |

## Packaging and Weights

|                           |   |
|---------------------------|---|
| <b>Packaging quantity</b> | 1 |
|---------------------------|---|

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>             |
|---------------|-----------------------------------|
| CHINA-ROHS    | Below maximum concentration value |
| ROHS          | Compliant                         |
| UK-ROHS       | Compliant                         |

