

CY7081-000 | FOSC-RSKG-16



FOSC® Gel Sealing Kit for round splice closure port, sealing 16 cables with diameter up to 3 mm

- Unique gel-based mechanical sealing option used on fiber splice closure ports for blown, standard, mini- and micro-cables
- Allows usage of multiple cable drops in a single closure outlet port, thus significantly increasing existing cable capacity
- Ideal for fiber cables with thin outer jackets that are difficult to seal with standard heat shrinkable sleeves

Product Classification

Regional Availability	EMEA
Product Type	Cable sealing
Product Brand	FOSC®
Product Series	FOSC 400G

General Specifications

Application	For use with FOSC-400G Fiber closures
Cable Capacity, maximum	16
Color	Black

Dimensions

Single Cable Diameter, maximum	3 mm 0.118 in
---------------------------------------	-----------------

Packaging and Weights

Included	Cable termination brackets Dummy plugs Multi-out gel seal
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

