

# D25359-000 | FOSC450-CABLE-TERM-4-BS



FOSC® 450 Cable Termination for Fiber Optic Splice Closure, BS closure only, 2 sets ea.: cbl retent. H/W, hose clamps; strength member

## Product Classification

|                              |                       |
|------------------------------|-----------------------|
| <b>Regional Availability</b> | North America         |
| <b>Product Type</b>          | Cable termination kit |
| <b>Product Brand</b>         | FOSC®                 |
| <b>Product Series</b>        | FOSC 450              |

## General Specifications

|                    |                                      |
|--------------------|--------------------------------------|
| <b>Application</b> | For use with FOSC-450 Fiber closures |
|--------------------|--------------------------------------|

## Packaging and Weights

|                           |   |
|---------------------------|---|
| <b>Packaging quantity</b> | 1 |
|---------------------------|---|

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>   |
|---------------|---|
| CHINA-ROHS    | Below maximum concentration value   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant   |
| UK-ROHS       | Compliant   |

