


FCM-7L0000-H1



FDF Fiber Termination Panel, 96 SC/APC, singlemode, 8 in x 23 in, putty white

Product Classification

| | |
|------------------------------|-------------------------------|
| Regional Availability | Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber patch panel |
| Product Series | FDF |

General Specifications

| | |
|----------------------------------|---|
| Functionality | Patching |
| Application | Used in rear-load FDF-style frames only |
| Body Style | Symmetrical |
| Color | Putty white |
| Color, front | Putty white |
| Growth Configuration | Fully loaded |
| Interface, front | SC/APC |
| Patch Cord Entry Location | Front, left side Front, right side |
| Rack Type | EIA 23 in |
| Rack Units | 4.57 |
| Shelf Movement | Fixed |
| Total Ports, quantity | 96 |

Dimensions

| | |
|---------------|------------------|
| Height | 203.2 mm 8 in |
| Width | 584.2 mm 23 in |
| Depth | 304.8 mm 12 in |

Material Specifications

| | |
|----------------------|---------------|
| Finish | Powder coated |
| Material Type | Steel |

FCM-7L0000-H1

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

