FL2-12TS350-B



FL2000 Fiber Termination/Splice Panel, unloaded, 12 Ports, 19 in, 2RU, black

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch/splice panel

Product Series FL2000

General Specifications

Functionality Patching | Splicing

Cable Exit LocationRear, left side | Rear, right side

Color Black

Growth ConfigurationUnloadedInterface, frontUnloadedRack TypeEIA 19 in

Rack Units 2

Shelf MovementHingedSplicing Capacity, maximum12Total Ports, quantity12

Dimensions

 Height
 88.9 mm | 3.5 in

 Width
 482.6 mm | 19 in

 Depth
 256.54 mm | 10.1 in

Material Specifications

Finish Powder coated

Material Type Steel



FL2-12TS350-B

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \text{ (-40 }^{\circ}\text{F to } +158 \,^{\circ}\text{F)}$ Storage Temperature $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \text{ (-40 }^{\circ}\text{F to } +185 \,^{\circ}\text{F)}$

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant/Exempted

