

FL2-12TS350



FL2000 Fiber Termination/Splice Panel, unloaded, 12 Ports, 2RU, 19 in, putty white

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	FL2000

General Specifications

Functionality	Patching Splicing
Cable Exit Location	Rear, left side Rear, right side
Color	Putty white
Growth Configuration	Unloaded
Interface, front	Unloaded
Rack Type	EIA 19 in
Rack Units	2
Shelf Movement	Hinged
Splicing Capacity, maximum	12
Total Ports, quantity	12

Dimensions

Height	88.9 mm 3.5 in
Width	482.6 mm 19 in
Depth	258.9 mm 10.193 in

Material Specifications

Finish	Powder coated
Material Type	Steel

FL2-12TS350

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Storage Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

