

FL2-48RPNL-B



FL2000 Fiber Termination Panel, unloaded, 48 Ports, 3RU, 19 in, black

Product Classification

| | |
|------------------------------|-------------------------------|
| Regional Availability | Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber patch panel |
| Product Series | FL2000 |

General Specifications

| | |
|-----------------------------------|-----------|
| Functionality | Patching |
| Color | Black |
| Color, front | Black |
| Growth Configuration | Unloaded |
| Interface, front | Unloaded |
| Patching Capacity, maximum | 48 |
| Rack Type | EIA 19 in |
| Rack Units | 3 |
| Shelf Movement | Hinged |
| Splicing Capacity, maximum | 0 |
| Total Ports, quantity | 48 |

Dimensions

| | |
|---------------|---------------------|
| Height | 133.35 mm 5.25 in |
| Width | 482.6 mm 19 in |
| Depth | 256.54 mm 10.1 in |

Material Specifications

| | |
|----------------------|---------------|
| Finish | Powder coated |
| Material Type | Steel |

Environmental Specifications

FL2-48RPNL-B

| | |
|------------------------------|--------------------------------------|
| Operating Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
| Storage Temperature | -40 °C to +85 °C (-40 °F to +185 °F) |

Packaging and Weights

| | |
|---------------------------|-------------------|
| Included | Mounting hardware |
| Packaging quantity | 1 |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

