


# FL2-C7J0072P2-6A00



FL2000 Fiber Termination/Splice Panel, pre-terminated with pigtails, 72 SC/APC, singlemode, 8RU, 19 in, putty white

## Product Classification

Regional Availability	Latin America   North America
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	FL2000

## General Specifications


Functionality	Patching   Splicing
Adapter Packs Included, quantity	12
Cable Exit Location	Rear, left side   Rear, right side
Color	Putty white
Growth Configuration	Fully loaded
Interface, front	SC/APC
Rack Type	EIA 19 in
Rack Units	8
Shelf Movement	Hinged
Splicing Capacity, maximum	72
Total Ports, quantity	72

## Dimensions

Height	355.6 mm   14 in
Width	482.6 mm   19 in
Depth	256.54 mm   10.1 in

## Ordering Tree

# FL2-C7J0072P2-6A00



## Material Specifications

Finish	Powder coated
Material Type	Steel

## Optical Specifications

Fiber Mode	Singlemode
------------	------------

## Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +85 °C (-40 °F to +185 °F)

## Packaging and Weights

Included	Mounting hardware
Packaging quantity	1

# FL2-C7J0072P2-6A00

---

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant/Exempted

