

# FL2-CDB0096PN-4A00



FL2000 Fiber Termination/Splice Panel, pre-terminated with pigtails, 96 LC/APC, singlemode, 5RU, 19 in, putty white

## Product Classification

Regional Availability	Latin America   North America
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	FL2000

## General Specifications


Functionality	Patching   Splicing
Adapter Packs Included, quantity	8
Cable Exit Location	Rear, left side   Rear, right side
Color	Putty white
Growth Configuration	Fully loaded
Interface, front	LC/APC
Rack Type	EIA 19 in
Rack Units	5
Shelf Movement	Hinged
Splicing Capacity, maximum	96
Total Ports, quantity	96

## Dimensions

Height	222.25 mm   8.75 in
Width	482.6 mm   19 in
Depth	256.54 mm   10.1 in

## Ordering Tree

# FL2-CDB0096PN-4A00



## Material Specifications

Finish	Powder coated
Material Type	Steel

## Optical Specifications

Fiber Mode	Singlemode
------------	------------

## Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +85 °C (-40 °F to +185 °F)

## Packaging and Weights

Included	Mounting hardware
Packaging quantity	1

# FL2-CDB0096PN-4A00

---

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

