# FL2-S780AG039-DU00



FL2000 Fiber Termination Panel, 144 LC/UPC, singlemode, 5RU, 23 in, putty white, pre-terminated with OSP cable, 39 meters, Stub tail at far end

#### **Product Classification**

Regional Availability Latin America | North America

Portfolio CommScope®

**Product Type** Fiber patch panel, with OSP cable

Product Series FL2000

#### General Specifications

**Functionality** Patching

Adapter Packs Included, quantity 12

Cable Exit Location Upward

Cable Stub Type IFC

**Color** Putty white

**Growth Configuration** Fully loaded

Interface, front LC/UPC

**Interface, rear** Stub tail

Rack Type EIA 23 in

Rack Units 5

Shelf Movement Hinged

Splicing Capacity, maximum 0

Total Ports, quantity 144

#### Dimensions

**Height** 222.25 mm | 8.75 in

**Width** 584.2 mm | 23 in


**Depth** 256.54 mm | 10.1 in

**Cable Length** 39 m | 127.953 ft



## FL2-S780AG039-DU00

### Ordering Tree



#### Material Specifications

**Finish** Powder coated

Material Type Steel

**Optical Specifications** 

**Fiber Mode** Singlemode

#### **Environmental Specifications**

**Operating Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

Storage Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights



# FL2-S780AG039-DU00

#### **Packaging quantity**

1

Compliant/Exempted

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted



**UK-ROHS**