FMT-DAS000021-A24B



FMT Fiber Splice Panel, with sliding tray, unloaded, 1RU, 19 in, black

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®
Product Type Fiber splice panel

Product Series FMT

General Specifications

Functionality Splicing

Body Style Symmetrical

ColorBlackColor, frontBlackGrowth ConfigurationUnloaded

Interface, front Unloaded

Patching Capacity, maximum 0

Rack Type EIA 19 in | EIA 23 in

Rack Units 1

Shelf Movement Sliding

Dimensions

 Height
 44.45 mm | 1.75 in


 Width
 482.6 mm | 19 in

 Depth
 279.91 mm | 11.02 in

Ordering Tree



FMT-DAS000021-A24B



Material Specifications

Finish Powder coated

Material Type Steel

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Ciassification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

