FPP-12SU-120M



HELIAX® Fiber Plug and Play 6 RRU Solution that will interface with Ericsson, Nokia, Huawei or ZTE RRU's, 120M

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Outdoor junction box

Product Brand HELIAX®

General Specifications

Application For use with Ericsson, Nokia, Huawei or ZTE remote radio units (RRU's)

Cable Entry LocationSideCable Entry, quantity, maximum, right3

Cable Entry, quantity, maximum, top 3

Color Gray

Mounting Pipe, 76.2–101.6 mm (3.0–4.0 in) OD | Wall

Dimensions

 Height
 406.4 mm | 16 in


 Width
 406.4 mm | 16 in

 Depth
 234.95 mm | 9.25 in

Outline Drawing



FPP-12SU-120M



Material Specifications

Material Type Aluminum

Environmental Specifications

Environmental SpaceIndoorOutdoorQualification StandardsIEC 60529:2001, IP67

Packaging and Weights

Included Mounting kit

Weight, net 11.299 kg | 24.91 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

COMMSCOPE®

FPP-12SU-120M





