FPX-2FRJA6-962



FPX Fiber Optic Termination Module, 2RU, 19in, Multimode, 96 fiber, LC Connector, putty white

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®
Product Type Fiber patch panel

Product Series FPX

General Specifications

Functionality Patching | Splicing

Adapter Packs Included, quantity 4

Body Style Symmetrical

Cable Exit Location Rear, left side | Rear, right side

Color Putty white

Growth Configuration Fully loaded

Interface, front LC/UPC

Rack Type EIA 19 in | EIA 23 in

Rack Units 2

Shelf Movement Sliding

Total Fibers, quantity 96

Total Ports, quantity 96

Dimensions

 Height
 88.9 mm | 3.5 in


 Width
 482.6 mm | 19 in

 Depth
 304.8 mm | 12 in

Ordering Tree



FPX-2FRJA6-962



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Multimode

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C to} +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to} +185 \,^{\circ}\text{F})$

Storage Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Packaging and Weights

Included Mounting hardware

COMMSCOPE®

FPX-2FRJA6-962

Packaging quantity

1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

UK-ROHS Compliant/Exempted

