## FPX-2FRP08-962



FPX Fiber Optic Termination/Splice Module, 2RU, 19in, Singlemode, 96 fiber, LC/UPC Connector, putty white

#### **Product Classification**

Regional Availability Latin America | North America

Portfolio CommScope®

**Product Type** Fiber patch/splice panel

Product Series FPX

General Specifications

Functionality Patching | Splicing

Adapter Packs Included, quantity 4

**Body Style** Symmetrical

 Cable Exit Location
 Rear, left side | Rear, right side

ColorPutty whiteColor, frontPutty whiteGrowth ConfigurationFully loadedInterface, frontLC/UPCPatching Capacity, maximum96

3 - 1 - 7

Rack Type EIA 19 in | EIA 23 in

Rack Units 2

**Shelf Movement** Sliding

**Splicing Type** Heat shrink, single fiber fusion

Total Fibers, quantity 96

Total Ports, quantity 96

Dimensions

 Height
 88.9 mm | 3.5 in


 Width
 482.6 mm | 19 in

 Depth
 304.8 mm | 12 in

Ordering Tree

**COMMSCOPE®** 

## FPX-2FRP08-962



### Material Specifications

**Finish** Powder coated

Material Type Steel

**Optical Specifications** 

Fiber Mode Singlemode

Fiber Type OS1

#### **Environmental Specifications**

Operating Temperature  $-40 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F}$ )

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F}$ )

Packaging and Weights

COMMSC PE°

# FPX-2FRP08-962

**Included** Mounting hardware

Packaging quantity 1

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

